

TECHSPEC®

30mm Dia. x 75mm FL, NIR II, Inked, Double-Convex Lens



Stock **#67-662-INK** 3-5 DAYS
[Other Coating Options](#)

- 1 +

C\$91.70

ADD TO CART

Qty 1-9
C\$91.70
Qty 10+
C\$82.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Back Focal Length BFL (mm):
73.35

Effective Focal Length EFL (mm): 75.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 4.96
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 76.67
Clear Aperture CA (mm): 29.00
f#: 2.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.20
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View