

TECHSPEC® 30mm Dia. x 75mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-373** ☐ In Stock
[Other Coating Options](#)

1 **C\$201.60**

ADD TO CART

Qty 1-5
C\$201.60
Qty 6+
C\$161.35
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Effective Focal Length EFL (mm):
75.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 67.44
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 29.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 11.40 ±0.20
Center Thickness CT 1 (mm) : 8.40 ±0.10
Center Thickness CT 2 (mm) : 3.00 ±0.10
Radius R₁ (mm) : 40.51
Radius R₂ (mm) : -38.68
Radius R₃ (mm) : -922.04
Edge Thickness ET (mm) : 8.40
Substrate : ☐ N-SSK6 / N-SF10
Surface Quality : 40-20
f/# : 2.5
Numerical Aperture NA : 0.20
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant