

[See all 19 Products in Family](#)

## 35mm f/4 HPi+ Lens 1.2"



Stock #29-286 **7 In Stock**

1  C\$1,288<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+ C\$1,288.00 each

Need More? [Request Quote](#)

### Product Downloads

#### General

HPi+ Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens **Imaging Lens Type:**

#### Physical & Mechanical Properties

Fixed **Iris Option:**

47.30 Length (mm):

34.5 Outer Diameter (mm):

4 Maximum Rear Protrusion (mm):

## Optical Properties

23.4° Horizontal Field of View @ Max Sensor Format:

22.8° Horizontal Field of View, 1.1" Sensor:

20.8° Horizontal Field of View, 1" Sensor:

14.3° Horizontal Field of View, 2/3" Sensor:

11.8° Horizontal Field of View, 1/1.8" Sensor:

10.5° Horizontal Field of View, 1/2" Sensor:

19.30 Maximum Image Circle (mm):

8 Number of Elements (Groups):

35.00 Focal Length FL (mm):

200 - ∞ Working Distance (mm):

FOV @ Max Sensor Format, H x V (mm):  
Horizontal: 23.5° Vertical: 20.4° Diagonal: 30.8°

f/4 Aperture (f/#):

M4 MgF2 Coating:

M4 MgF2 Coating Specification:

20.61 Entrance Pupil Position (mm):

31.10 Object Space Principal Plane (mm):

-22.60 Image Space Principal Plane (mm):

0.37 Maximum Distortion (%):

-35.62 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

VIS Wavelength:

## Sensor

1.2" Maximum Sensor Format:

2.74 Pixel Size (µm):

## Threading & Mounting

M25.5 x 0.50 Filter Thread:

C-Mount Mount:

## Environmental & Durability Factors

-20 to +60 Storage Temperature (°C):

Industrial (Fixed Aperture with Simplified Mechanics) Type of Ruggedization:

## Regulatory Compliance

View Certificate of Conformance:

## Product Details

- Instrumentation (HPI+) versions of our HP+ Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 1.2", C-Mount Lenses
- Up to 24.5 MegaPixels, 2.74µm Pixel Size Sensors
- 16mm to 35mm Focal Length

TECHSPEC® HPI+ Series Fixed Focal Length Lenses are designed to provide exceptional performance for the harsh demands of factory automation (FA) and machine vision. These lenses are designed for use with Sony's 4th Generation Pregius S™ 24.5MP 1.2" IMX530 and IMX540 sensors. The f/2.8 aperture provide increased light throughput and high-resolution performance. TECHSPEC® HPI+ Series Fixed Focal Length Lenses are C-Mount and are designed without an iris or focusing mechanism to drive down size, weight, and cost. These lenses are ideal for measurement and gauging, 3D stereo vision, and object tracking.

HP+ Series: Features locking focus and iris rings to prevent unwanted adjustments and are designed for factory automation.

**HP Series:** Features locking cam focus and iris adjustment. This is the most adjustable version of these optical designs and is the typical high-quality machine vision lens.

**HPI Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.

**HPi Series:** All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.