

[See all 10 Products in Family](#)

330mm, 515-540nm JENar™ F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock **#16-774** **7 In Stock**

⊖ 1 ⊕ C\$2,135⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,135.00 each
Need More?	Request Quote

Product Downloads

General

017700-208-26 **Model Number:**

JENar F-Theta **Type:**

Note:
Damage Warning: Not recommended for picosecond and femtosecond laser pulses.

Protective Window:
[#17-685](#): One Included

Manufacturer:

Physical & Mechanical Properties

119.8 +0/-0.2 **Maximum Diameter (mm):**

1300 **Weight (g):**

426.1 **Flange Distance (mm):**

16 **Input Beam Diameter, 1/e² (mm):**

62.1 **Maximum Length (mm):**

Optical Properties

330.00 **Focal Length FL (mm):**

57.6 **Scan Angle (°):**

245 x 245 **Scan Field (mm):**

F-Theta Only: 18.4
With Scanner: 18.4 **Telecentricity (°):**

384.1 **Working Distance (mm):**

515 - 540 **Wavelength Range (nm):**

Damage Threshold, By Design:
2.5 J/cm² * (τ/[ns])^{0.35}
2.5 MW/cm²

347 **Scan Field Diameter (mm):**

23 **Focus Size Diameter, 1/e² (μm):**

6810 **GDD Specification (fs²):**

2.5 J/cm² * (τ/[ns])^{0.35} **Damage Threshold, Pulsed:**

2.5 MW/cm² **Damage Threshold, CW:**

Threading & Mounting

M85 x 1 **Mounting Threads:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 320mm x 320mm
- Wide Range of Focal Lengths from 108mm - 330mm
- [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ F-Theta Scanning Lenses are designed to provide flat field at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta lenses feature a wide range of focal lengths and large scan fields. Optimized for common Nd:YAG, Yb:doped, and fiber laser sources, these lenses are available in wavelength ranges of 355nm, 515-540nm, and 1030-1080nm. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ F-Theta Scanning Lenses are ideal for high-precision laser material processing and laser scanning applications.

[Contact us](#) if your application requires Jenoptik JENar™ F-Theta Scanning Lenses or [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) not shown on our website.