

**TECHSPEC® 35mm N-SF11 MgF<sub>2</sub> Coated Equilateral Prism**



Equilateral Prisms

Stock #47-284 **4 In Stock**

⊖ 1 ⊕ C\$368<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$368.20 each
Qty 6-25	C\$294.00 each
Qty 26-49	C\$276.15 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Equilateral Prism **Type:**

**Physical & Mechanical Properties**

35.00 **Length of Face (mm):**

35.00 **Length (mm):**

Dimensional Tolerance (mm):

±0.1

## Optical Properties

MgF<sub>2</sub> (400-700nm) **Coating:**

**N-SF11** **Substrate:**

40-20 **Surface Quality:**

±2 **Angle Tolerance (arcmin):**

Dispersion **Image Orientation:**

R<sub>avg</sub> ≤ 1.75% @ 400 - 700nm **Coating Specification:**

400 - 700 **Wavelength Range (nm):**

2.50 **Power (fringes) @ 632.8nm:**

0.50 **Irregularity (fringes) @ 632.8nm:**

## Regulatory Compliance


**View** **Certificate of Conformance:**

## Product Details

- Ideal for Light Dispersion
- Sizes Ranging from 5 - 50mm
- Available Uncoated or Anti-Reflection Coated
- Additional [Equilateral Prism](#) Options Available

TECHSPEC® Equilateral Prisms feature three equal 60° angles and are often referred to as dispersing prisms. Equilateral prisms are ideal for wavelength separating applications and light dispersion. These prisms are available in sizes ranging from 5-50mm. Our TECHSPEC® Equilateral Prisms are offered uncoated or with a single layer MgF<sub>2</sub> anti-reflection coating. Additional [Equilateral Prism](#) options are available.

## Technical Information



## Coating Curves