

TECHSPEC® 35 x 50mm Protected Gold, 4-6λ Mirror



Stock **#48-455** ☐ In Stock

1

C\$99.40

ADD TO CART

Qty 1-5

C\$99.40

Qty 6+

C\$79.10

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):
35.0 x 50.0

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 33.25 x 47.50
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 50.00
Width (mm): 35.00
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant