

[See all 7 Products in Family](#)

# 38.1mm Dia. x 200mm FL, Uncoated, ISP Optics Zinc Selenide (ZnSe) PCX Lens | ZC-PX-38-200

See More by [ISP Optics](#)



Zinc Selenide Plano-Convex (PCX) Lenses



Stock **#24-956** CLEARANCE **5 In Stock**

C\$439<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1+	C\$439.60 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Type:  
Plano-Convex Lens

Model Number:  
ZC-PX-38-200

**Physical & Mechanical Properties**

38.10 +0.00/-0.13	<b>Diameter (mm):</b>
Protective as needed	<b>Bevel:</b>
2.60 ±0.20	<b>Center Thickness CT (mm):</b>
<3	<b>Centering (arcmin):</b>
34.29	<b>Clear Aperture CA (mm):</b>
2.00	<b>Edge Thickness ET (mm):</b>

## Optical Properties

200.00 @ 10.6µm	<b>Effective Focal Length EFL (mm):</b>
Zinc Selenide (ZnSe), CVD Grade	<b>Substrate:</b> <input type="checkbox"/>
5.25	<b>f#:</b>
0.10	<b>Numerical Aperture NA:</b>
Uncoated	<b>Coating:</b>
600 - 18000	<b>Wavelength Range (nm):</b>
199.39	<b>Back Focal Length BFL (mm):</b>
±2	<b>Focal Length Tolerance (%):</b>
281.20	<b>Radius R<sub>1</sub> (mm):</b>
60-40	<b>Surface Quality:</b>
λ/20	<b>Irregularity (P-V) @ 10.6µm:</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 240:</b>

## Product Details

- Low Dispersion and Absorption from 0.6 – 18µm
- High Resistance to Thermal Shock
- Uncoated or BBAR Coated for 8 – 12µm

ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are ideal for focusing or collimation of light in the Mid-Wave Infrared (MMR) and Long-Wave Infrared (LWR) spectrum. Featuring low absorption and high resistance to thermal shock, ZnSe is widely used in high power CO<sub>2</sub> laser systems. ZnSe is not recommended for harsh environments as it is a relatively soft material that scratches easily, and only has a Knoop Hardness of 120. ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are available either uncoated or Broadband Anti-Reflection (BBAR) coated for increased transmission from 8-12µm.

**Note:** Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools