

TECHSPEC<sup>®</sup> 35mm Enhanced Aluminum Coated, N-BK7 Right Angle Mirror



Stock **#49-406** 20+ In Stock

-

1

+

C\$253<sup>.40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$253.40 each                |
| Qty 6-25       | C\$203.00 each                |
| Qty 26-49      | C\$189.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Right Angle Mirror

Type:

Physical & Mechanical Properties

35.00Length of Legs (mm):


±0.1Dimensional Tolerance (mm):

|                                     |                                   |
|-------------------------------------|-----------------------------------|
| Protective as needed                | Bevel:                            |
| 44.55 x 31.50                       | Clear Aperture CA (mm):           |
| 49.50                               | Length of Hypotenuse (mm):        |
| Optical Properties                  |                                   |
| N-BK7                               | Substrate: □                      |
| 40-20                               | Surface Quality:                  |
| R <sub>avg</sub> >95% @450 - 650nm  | Coating Specification:            |
| Enhanced Aluminum (450-650nm)       | Coating:                          |
| Metal                               | Coating Type:                     |
| ±2                                  | Angle Tolerance (arcmin):         |
| 0.45 - 0.65                         | Wavelength Range (µm):            |
| 450 - 650                           | Wavelength Range (nm):            |
| 0.2 J/cm <sup>2</sup> @ 532nm, 10ns | Damage Threshold, Reference: □    |
| 1.25                                | Power (fringes) @ 632.8nm:        |
| 0.50                                | Irregularity (fringes) @ 632.8nm: |
| Regulatory Compliance               |                                   |
| Compliant                           | RoHS 2015:                        |
| Compliant                           | Reach 219:                        |
| View                                | Certificate of Conformance:       |

## Product Details

- Reflects Light at 90°
  - Ideal for System Alignment
  - Enhanced Aluminum, Protected Gold, and Protected Silver Coatings
- TECHSPEC® Right Angle Mirrors are available with enhanced aluminum, protected gold, or protected silver coatings. These coatings allow for improved handling of the component, increased durability of the metal coating, and protection from oxidation with little impact on the performance of the metal coating. The mirrors are designed with an N-BK7 substrate. Right angle mirrors reflect incident light at 90°, are easily mounted, and are crucial in many optical systems. TECHSPEC® Right Angle Mirrors are ideal for applications requiring precision alignment and high performance.

## Technical Information



## Coating Curves

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---