

TECHSPEC® 3.5mm, f/2 Ci Series Fixed Focal Length Lens



3.5mm Focal Length

Stock **#87-545** ☐ In Stock

- 1 + **C\$707.00**

ADD TO CART

Qty 1-24

C\$707.00

Qty 25+

C\$637.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Fixed

Length (mm):
39.38

Horizontal Field of View, 1/2" Sensor:
29.5mm - 87.2°

Filter Thread:

M105 x 1.00 with required adapter [#89-848](#)

Maximum Diameter (mm): 50
Weight (g): 97
Horizontal Field of View, 1/3" Sensor: 23.0mm - 74.4°
Maximum Rear Protrusion (mm): 2.64
Maximum Image Circle (mm): 9.00
Numerical Aperture NA, Object Side: 0.0572
Horizontal Field of View @ Max Sensor Format: 41.2mm - 102.8°
Number of Elements (Groups): 8 (7)
Horizontal Field of View, 1/1.8" Sensor: 41.2mm - 102.8°
Front Thread: M50.0 x 0.5 (Male)
Type: Fixed Focal Length Lens
Diameter (mm): 26.50
Focal Length FL (mm): 3.50
Primary Magnification PMAG: 0.236
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 0 - ∞
Mount: C-Mount
Aperture (f/#): f/2
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 15.27
Horizontal Field of View, 1/4" Sensor: 16.3mm - 57.4°
Object Space Principal Plane (mm): 18.31
Image Space Principal Plane (mm): 7.49
Field of View at Max Sensor Format: Horizontal: 41.2mm - 102.4° Vertical: 26.8mm - 82.3° Diagonal: 63.5mm - 117.1°
Maximum Distortion (%): -20.95
Exit Pupil Position (mm): -15.28
Lens Wavelength Range: VIS
Imaging Lens Type: Compact Lens with Fixed Aperture
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View