

TECHSPEC® 12.5mm Dia. x 25.0mm FL, NIR II Coated, Plano-Convex Lens



Stock **#38-401** ☐ In Stock
[Other Coating Options](#)

1 **C\$56.70**

ADD TO CART

Qty 1-9
C\$56.70
Qty 10+
C\$51.10
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Back Focal Length BFL (mm): 22.96
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.10 ±0.05
Edge Thickness ET (mm): 1.49
Radius R₁ (mm): 12.92
Clear Aperture CA (mm): 11.5
f#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant