

TECHSPEC® 15.0mm Dia. x 50.0mm FL, VIS-EXT Coated, Plano-Convex Lens



Stock **#38-467** ☐ In Stock
[Other Coating Options](#)

1 **C\$61.60**

ADD TO CART

Qty 1-9
C\$61.60
Qty 10+
C\$55.30
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
50.00 @ 587.6nm

Back Focal Length BFL (mm): 48.35
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.10
Edge Thickness ET (mm): 1.39
Radius R₁ (mm): 25.84
Clear Aperture CA (mm): 14
f/#: 3.33
Numerical Aperture NA: 0.15
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant