

[See all 61 Products in Family](#)

38 x 38mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#46-652** 20+ In Stock

-

1

+

C\$43⁰⁵

ADD TO CART

Volume Pricing	
Qty 1-5	C\$43.05 each
Qty 6-25	C\$33.60 each
Qty 26-99	C\$28.00 each
Need More?	Request Quote

Product Downloads

General	
Flat Mirror	Type:
Physical & Mechanical Properties	
38.0 x 38.0 ±0.76	Dimensions (mm):
Protective as needed	Bevel:

>90	Clear Aperture (%):
1.00	Thickness (mm):
38.00	Length (mm):
38.00	Width (mm):

Optical Properties

4 - 6λ	Surface Flatness (P-V):
Float Glass	Substrate: ☐
80-50	Surface Quality:
R _{avg} >85% @400 - 700nm	Coating Specification:
Protected Aluminum (400-700nm)	Coating:
Metal	Coating Type:
45.00	Angle of Incidence (°):
400 - 700	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


Product Details

- Wide Variety of Shapes and Sizes Available
- >85% Reflection of Visible Light
- [Contact Us](#) for Custom Sizes

4 - 6λ First Surface Mirrors are an economical choice for a wide range of applications. First surface mirrors feature high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in circular, square, and rectangular dimensions. Rectangular 4 - 6λ First Surface Mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. The mirrors have a protected aluminum coating, and they reflect greater than 85% of visible light.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts