


TECHSPEC® 38.1 x 25.4mm 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-650** ☐ In Stock



1



C\$249.20

ADD TO CART

Qty 1-5

C\$249.20

Qty 6+

C\$219.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

85
Back Surface: Commercial Polish
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} >99.8% @ 532nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (532nm)
Design Wavelength DWL (nm): 532
Dimensions (mm): 38.1 x 25.4 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View