

TECHSPEC® 3mm, Alum. & AR Coated, N-SF11 Micro Right Angle Prism



N-SF11 Right Angle Prisms

Stock **#47-923** ☐ In Stock

1 **C\$208.60**

ADD TO CART

Qty 1-5

C\$208.60

Qty 6+

C\$187.74

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
MgF₂ & Aluminized

Substrate: ☐
[N-SF11](#)

Surface Quality:
20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.05
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 4.20
Length of Legs (mm): 3.00
Image Orientation: Left-Handed
Coating Specification: Legs: R _{avg} ≤1.75% @ 400 - 700nm Hypotenuse: R _{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/4
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @532nm & 1064nm, 10ns Legs: 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant