

TECHSPEC® 3" Dia, 12" FL Protected Alum., Spherical Mirror



Stock **#49-604** ☐ In Stock

- 1 + **C\$322.00**

ADD TO CART

Qty 1-9
C\$322.00
Qty 10+
C\$273.70
Volume Pricing
Request Quote

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy:

M4
Diameter (inches): 3.0
Diameter (mm): 76.20 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 12.00
Effective Focal Length EFL (mm): 304.80
Radius of Curvature (mm): 609.60
Aperture (f/#): f/4
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant