

TECHSPEC®

12.5mm Dia. x 15mm FL, NIR II Coated, Plano-Convex Lens



Stock **#38-398** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$58.10

ADD TO CART

Qty 1-9
C\$58.10
Qty 10+
C\$52.15
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Back Focal Length BFL (mm): 13.26
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.10 ±0.05
Edge Thickness ET (mm): 1.30
Radius R₁ (mm): 11.77
Clear Aperture CA (mm): 11.5
f#: 1.2
Numerical Aperture NA: 0.42
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant