

LED IR 4-Bar Square Light Unit 940nm

See More by [CCS](#)



LED IR 4-Bar Square Light Unit 940nm

Stock **#21-848** **1 In Stock**

-

1

+

C\$4,613^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$4,613.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
LDQ-150IR2-940	Model Number:
LED Illuminator	Type of Illumination:
CCS	Manufacturer:
Bar Light	Geometry:

Illumination Mode:		Constant
Physical & Mechanical Properties		
Dimensions (mm):		W 148 mm x D 148 mm x H 30.2mm
Weight (g):		530
Optical Properties		
Color:		IR
Wavelength (nm):		940
Electrical		
Power Consumption (W):		16
Hardware & Interface Connectivity		
Input Voltage (V):		24
Power Supply:		Power Supply Required and Sold Separately. USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491
Regulatory Compliance		
RoHS 2015:		Exempt
Reach 224:		Contains SVHC(s)
Certificate of Conformance:		View

Product Details

- 850 or 940nm Wavelength Options
- Compact Lightweight Housing
- Single and 4-Bar Configurations Available

CCS Infrared (IR) Bar Lights provide uniform infrared illumination along a localized area. Designed with a compact lightweight housing, these bar lights can be easily integrated into applications with a limited working area. CCS Infrared (IR) Bar Lights are ideal for a variety of testing and inspection applications in industrial and manufacturing environments such as foreign material detection, color reduction in monochromatic images, and character isolation for optical character recognition (OCR). These bar lights are available as a single bar light or as a 4-bar square configuration with both options featuring adjustable output angles. Compared to visible light, infrared light provides a lower scattering rate and a higher transmittance rate, allowing for fewer surface reflections and deeper penetration into materials for imaging.

Technical Information

