

TECHSPEC® 9.0mm Dia. x 10mm FL, YAG-BBAR, Inked, Plano-Convex Lens



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock **#38-571-INK** 3-5 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

C\$72.10

ADD TO CART

Qty 1-9

C\$72.10

Qty 10+

C\$64.75

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 ±0.025

Effective Focal Length EFL (mm):

10.00 @ 587.6nm
Back Focal Length BFL (mm): 8.49
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 2.70 ±0.05
Edge Thickness ET (mm): 1.28
Radius R₁ (mm): 7.85
Clear Aperture CA (mm): 8.1
f/#: 1.11
Numerical Aperture NA: 0.45
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 500 - 1100
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View