

405nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#12-276** ☐ **In Stock**

[Additional Bandwidths](#)

-

1

+

C\$1,071.70

ADD TO CART

Qty 1+
C\$1,071.70

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Bandwidth (nm):
1.5

OD 5 Blocking Wavelength Range (nm) :
353.5 - 401 & 409.1 - 495.3

OD 6 Blocking Wavelength Range (nm):

372.6 - 398.9 & 411.1 - 445.5
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): ≥22
Center Wavelength CWL (nm): 405.00
Design Wavelength DWL (nm): 405
Full Width-Half Max FWHM (nm): 1.50 - 2.8
Substrate: ☐ Low Fluorescence N-BK7 or equivalent
Minimum Transmission (%): >90
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.10
Transmission (%): >90
Type: Bandpass Filter
Blocking Wavelength Range (nm): 353.5 - 401 & 409.1 - 495.3
Construction: Mounted in Black Anodized Ring
Environmental Durability: ML-STD-810F Paragraphs 501.4, 502.4, and 507.4
Physical Durability: ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.0 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View