

[See all 12 Products in Family](#)

3mm Diameter, Extended B270 Half-Ball Lens



B270 Half-Ball Lenses

Stock **#21-898** **3 In Stock**

C\$51⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-10 | C\$51.80 each |
| Qty 11-25 | C\$43.75 each |
| Qty 26-49 | C\$39.20 each |
| Need More? | Request Quote |

Product Downloads

General

Half-Ball Lens **Type:**

Physical & Mechanical Properties

3.00 ±0.1 **Diameter (mm):**

1.80 ±0.15 **Center Thickness CT (mm):**

1.50

Radius R (mm):

Optical Properties

B270

Substrate:

Uncoated

Coating:

360 - 2700

Wavelength Range (nm):

1.523

Index of Refraction (n_d):

Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 224:

[View](#)

Certificate of Conformance:

Product Details

- Available in Truncated and Extended Geometries
- High Transmission in the Visible and NIR
- Ideal for Cost Sensitive Applications

B270 Half-Ball Lenses feature a molded spherical surface and polished plano surface, facilitating easier mounting compared to ball lenses. The B270 substrates have high transmission from the visible to the near infrared (NIR) and have a similar refractive index to N-BK7, making these lenses an ideal alternative for cost sensitive applications. Each diameter of lens is available in two form factors, truncated (hypo-hemisphere) and extended (hyper-hemisphere), providing options to best meet system mechanical requirements. B270 Half-Ball Lenses are used in high power LED, fiber coupling, endoscopy, microscopy, and laser measurement applications.