

TECHSPEC®

40mm Dia. x 200mm FL, NIR II Coated, Double-Convex Lens



Stock **#33-418** ☐ In Stock

[Other Coating Options](#)

1

C\$87.50

ADD TO CART

Qty 1-9
C\$87.50
Qty 10+
C\$78.75
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Back Focal Length BFL (mm):
197.35

Effective Focal Length EFL (mm): 200.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 8.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 6.05
Radius R₁=R₂ (mm): 205.35
Clear Aperture CA (mm): 39.00
f#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant