

[See all 33 Products in Family](#)

**TECHSPEC® 40mm Dia x 40mm FL, Uncoated, High Precision Aspheric Lens**



TECHSPEC® High Precision Aspheric Lenses

Stock **#12-445** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **C\$1,328<sup>60</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>C\$1,328.60</b> each
Qty 6-10	<b>C\$1,195.60</b> each
Qty 11+	<b>C\$1,115.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens **Type:**

3D Surface Profile included with uncoated lenses **Note:**

**Physical & Mechanical Properties**

**Diameter (mm):**

40.00 +0.00/-0.025

Centering (arcmin):  
<1

Clear Aperture CA (mm):  
36.00

Edge Thickness ET (mm):  
6.83

Center Thickness CT (mm):  
14.70

Bevel:  
Protective as needed

Shape of Back Surface:  
Plano

## Optical Properties

Effective Focal Length EFL (mm):  
40.00 @ 587.6nm

Numerical Aperture NA:  
0.50

Back Focal Length BFL (mm):  
31.21

Substrate:   
N-SF5

Aspheric Design Wavelength (nm):  
587.6

Asphere Figure Error, RMS @ 632.8nm:  
λ/40

Coating:  
Uncoated

Surface Quality:  
40-20

f#:  
1

Wavelength Range (nm):  
380 - 2500

Conjugate Distance:  
Infinite

Power (diopters):  
25.00

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Precision Aspheric Surface
- 3D Surface Profiles Included with Uncoated Lenses
- Uncoated and <0.25% Reflectance V-Coat Available

TECHSPEC® High Precision Aspheric Lenses guarantee better than λ/40 wave aspheric figure error. Achieved via precision magneto-rheological finishing (MRF), these aspheres offer high numerical apertures with diameters ranging from 15 to 50mm and are ideal for a variety of imaging and low light level applications. Each TECHSPEC High Precision Aspheric Lens is individually measured. 3D surface profiles are included with uncoated lenses. For diffraction-limited aspheres designed at specific Nd:YAG laser wavelengths, see our [TECHSPEC High Precision Laser Grade Aspheric Lenses](#).

## Compatible Mounts