

[See all 21 Products in Family](#)

4.0mm Diameter, Sapphire Half-Ball Lens



Stock **#49-555** 12 In Stock

-

1

+

C\$47^{.25}

ADD TO CART

Volume Pricing	
Qty 1-10	C\$47.25 each
Qty 11-49	C\$37.80 each
Need More?	Request Quote

Product Downloads

General

Type:

Half-Ball Lens

Physical & Mechanical Properties

Diameter (mm):

4.00

Radius R (mm):

2.00

Specific Gravity (g/cm³):

3.98

2.00	Thickness (mm):
300,000	Compressive Strength (psi):
±2.54	Diameter Tolerance (µm):

Optical Properties

Sapphire (Al ₂ O ₃)	Substrate: ☐
Uncoated	Coating:
1.77	Index of Refraction (n _d):
0.64	Sphericity (µm):

Environmental & Durability Factors

2053.00	Melting Temperature (°C):
---------	---------------------------


Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Excellent for Severe Environments
 - High Chemical Stability
 - Sapphire and Ruby Ball Lenses Also Available
- Sapphire and Ruby Half-Ball Lenses feature a very short back focal length with the convenience of a flat surface for easy mounting. Sapphire features a high index of refraction and excellent broadband transmission characteristics. Ruby half-ball (hemispherical) lenses are easier to see and, therefore, easier to handle for physical applications. Sapphire and Ruby Half-Ball Lenses are very chemically stable and are great for severe environments, high-temperature applications, and applications requiring high melting points. Typical applications include fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).