

[See all 6 Products in Family](#)

## 40mm Sq. Metric Kinematic Magnetic Base



#22-406: 40mm Sq. Metric Kinematic Magnetic Base

Stock **#22-406** **4 In Stock**

- 1 + C\$152<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	C\$152.60 each
Qty 10+	C\$138.32 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Metric **Type:**  
No **Switchable:**

#### Physical & Mechanical Properties

40.00 **Length (mm):**  
**Width (mm):**

40.00

Thickness (mm):

25.40

Construction:

Anodized Aluminum

Weight (kg):

0.08

Repeatability ( $\mu$ rad):

<70.0

## Threading & Mounting

Mounting Threads:

(4) M2 x 0.4, (4) M3 x 0.5, (2) M4 x 0.7 (1) M6 x 1.0

## Material Properties

Magnetic Force (N):

10

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

## Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.