

TECHSPEC® 45° AOI, 25.0mm Diameter, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-447** **20+ In Stock**

C\$84⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$84.00 each
Qty 10-25	C\$75.60 each
Qty 26-49	C\$72.10 each
Need More?	Request Quote

Product Downloads

General

Cold Mirror Type:

Physical & Mechanical Properties

25.00 Diameter (mm):

3.30 ±0.2 Thickness (mm):

Dimensional Tolerance (mm):

+0.0/-0.2

Optical Properties

Dichroic Filter **Transmission (%)**:

Dielectric **Coating Type**:

Cold Mirror, 45° **Coating**:

4 - 6λ **Surface Flatness (P-V)**:

425 - 1150 **Wavelength Range (nm)**:

Substrate:
BOROFLOAT®

45 **Angle of Incidence (°)**:

Coating Specification:
R_{avg} ≥95% @ 400 - 690nm and T_{avg} ≥90% @ 750 - 1200nm
AR Coating: R_{avg} <1% @ 700 - 1150nm

80-50 **Surface Quality**:

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View



Reach 247:
Compliant

Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information



Quote Your Size

Compatible Mounts