

TECHSPEC® 40mm Dia. x 60mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-379** ☐ In Stock
[Other Coating Options](#)

1 **C\$252.00**

ADD TO CART

Qty 1-5
C\$252.00
Qty 6+
C\$201.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):
60.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 50.29
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 39.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 17.46 ±0.20
Center Thickness CT 1 (mm) : 14.46 ±0.10
Center Thickness CT 2 (mm) : 3.00 ±0.10
Radius R₁ (mm) : 37.33
Radius R₂ (mm) : -31.54
Radius R₃ (mm) : -124.51
Edge Thickness ET (mm) : 10.03
Substrate : ☐ N-SK11 / N-SF5
Surface Quality : 40-20
f/# : 1.5
Numerical Aperture NA : 0.33
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View