

TECHSPEC®

4.0mm Dia. x 8.0mm FL, NIR I Coated, Plano-Convex Lens



Stock **#48-704** ☐ In Stock

[Other Coating Options](#)

1

C\$81.20

ADD TO CART

Qty 1-9
C\$81.20
Qty 10+
C\$73.15
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
4.00 +0.0/-0.025

Effective Focal Length EFL (mm):
8.00 @ 587.6nm

Back Focal Length BFL (mm): 7.17
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BAF10
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.39 ±0.05
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 5.36
Clear Aperture CA (mm): 3.6
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant