


LightPath 357765 | 6.33mm Dia., 0.61 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-681** ☐ In Stock

-

1

+

C\$133.00

ADD TO CART

Qty 1-10
C\$133.00
Qty 11+
C\$116.90
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 6.33 ±0.015
Effective Focal Length EFL (mm): 4.00 @ 488nm
Numerical Aperture NA:

0.61
Substrate: D-Lak6
Aspheric Design Wavelength (nm): 488
Coating: BBAR (350-600nm)
Coating Specification: R _{abs} <1.0% @ 350 - 600nm
Surface Quality: 20-10
Clear Aperture CA (mm): 4.80
Edge Thickness ET (mm): 1.57
Center Thickness CT (mm): 2.92 ±0.05
f#: 0.82
Bevel: Protective bevel as needed
Lightpath Lens Code: 357765
Type: Aspheric Lens
Wavelength Range (nm): 350 - 600
Working Distance (mm): 2.37
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant