


LightPath 356785 | 2.75mm Dia., 0.62 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-679** CLEARANCE CONTACT US

-

1

+

C\$61.53

ADD TO CART

Qty 1+

C\$61.53

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
2.75 ±0.015

Effective Focal Length EFL (mm):
1.42 @ 488nm

Numerical Aperture NA:
0.62

Substrate: [L-LAL12](#)

Aspheric Design Wavelength (nm): 488
Coating: BBAR (350-600nm)
Coating Specification: R _{abs} <1.0% @ 350 - 600nm
Surface Quality: 20-10
Clear Aperture CA (mm): 1.70
Edge Thickness ET (mm): 0.6
Center Thickness CT (mm): 1.08 ±0.05
f/#: 0.81
Bevel: Protective bevel as needed
Lightpath Lens Code: 356785
Type: Aspheric Lens
Wavelength Range (nm): 350 - 600
Working Distance (mm): 0.86
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant