

Coherent® Diamond Series CO₂ Laser 1322624 | 40W

See More by [Coherent®](#)



Coherent® Diamond C-Series CO₂ Laser

Stock **#37-078** **2 In Stock**

-

1

+

C\$10,647^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$10,647.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



SPECIFICATIONS

General

Air

Cooling Method:

Note:

Max. Case Temperature: 60°C	
IV	Laser Class - CDRH:
1322624	Model Number:
Physical & Mechanical Properties	
425 x 92.5 x 154.5	Dimensions (mm):
15	Weight (lbs):
Optical Properties	
>100:1	Polarization:
10,600.00	Wavelength (nm):
<1.3	Mode Quality, M²:
±0.5	Beam Diameter Tolerance (mm):
3.6	Beam Diameter (mm):
<5	Beam Divergence (mrad):
Infrared	Color:
10,550 - 10,630	Bandwidth (nm):
Electrical	
±5	Power Stability (%):
40	Output Power (W):
0 to 100% DC	Operating Duty Cycle:
0 to 100	Frequency (kHz):
Hardware & Interface Connectivity	
Power Supply Required and Sold Separately: USA: #17-206 Europe: #17-206 Japan: #17-206 Korea: # China: #17-206	Power Supply:
Free Space	Output Type:
Environmental & Durability Factors	
5 to 40	Operating Temperature (°C):
-10 to +60 Non-Condensing	Storage Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Superior Beam Quality and Power Stability for Improved Process Quality
 - Fully Sealed Integrated Package with Built-in RF Power Supply
 - Wide Power Range with CW or Pulse Width Modulation Control
- Coherent® Diamond C-Series CO₂ Lasers offer reliability with more than 50k operating hours, along with superior beam quality and stability. These lasers are ideal for a wide range of applications from marking and engraving to material processing. Coherent® Diamond C-Series CO₂ Lasers offer a compact option with an integrated RF power supply. Maximum output power ranges from 20 to 40 watts, and can be controlled through pulse width modulation (PWM).
- Note:** Power supply ([#17-206](#)) and Controller ([#37-079](#)) are required for operation.

