

## 4.25μm 25mm Diameter, IR Shortpass Filter



Stock #21-255 12 In Stock

-

1

+

C\$688<sup>.58</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$688.58 each                |
| Qty 6-25       | C\$620.31 each                |
| Qty 26-49      | C\$589.15 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

### SPECIFICATIONS

#### General

Type:

Shortpass Filter

#### Physical & Mechanical Properties

|                                    |                                     |
|------------------------------------|-------------------------------------|
| 25.00 +0.0/-0.2                    | Diameter (mm):                      |
| 1.00 ±0.2                          | Thickness (mm):                     |
| Optical Properties                 |                                     |
| 0                                  | Angle of Incidence (°):             |
| ≥3.0                               | Optical Density OD (Average):       |
| 4,250.00                           | Cut-Off Wavelength (nm):            |
| 4.25                               | Cut-Off Wavelength (μm):            |
| Silicon                            | Substrate: <input type="checkbox"/> |
| 4510 - 7000                        | Rejection Wavelength (nm):          |
| 80-50                              | Surface Quality:                    |
| ≥85                                | Transmission (%):                   |
| 3300 - 4150                        | Transmission Wavelength (nm):       |
| 3.3 - 4.15                         | Transmission Wavelength (μm):       |
| ±2                                 | Cut-Off Tolerance (%):              |
| 4.51 - 7                           | Rejection Wavelength (μm):          |
| Environmental & Durability Factors |                                     |
| ML-C-48497A, Section 4.5.3         | Durability:                         |
| Regulatory Compliance              |                                     |
| <a href="#">View</a>               | Certificate of Conformance:         |

## PRODUCT DETAILS

- ≥85% Average Transmission over a Broad Infrared Wavelength Range
  - OD ≥3.0 Blocking Across Rejection Band
  - Common Wavelengths for Environmental and Medical Applications
- Infrared (IR) Shortpass Filters are designed to provide ≥85% average transmission across their transmission band and OD ≥3.0 blocking across their rejection band. With cut-off wavelengths ranging from 3.95 to 13.3μm, these shortpass filters provide coverage across the IR spectrum. Featuring durable coatings and optical-quality Silicon and Germanium substrates, these filters can withstand normal cleaning and handling associated with high-quality optical components. Infrared (IR) Shortpass Filters are ideal for a wide range of imaging and detection applications in environmental sciences, life sciences, and medical diagnostics. These filters can be used in combination with [Infrared \(IR\) Longpass Filters](#) to create custom bandwidth filters and fine tune optical systems.

## SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

