

TECHSPEC® 50 x 50 x 3.3mm Thickness, NIR Coated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock #12-194 11 In Stock

-

1

+

C\$80⁻¹⁴

ADD TO CART

Volume Pricing	
Qty 1-5	C\$80.14 each
Qty 6-25	C\$63.81 each
Qty 26-99	C\$58.62 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Protective Window

Type:


Physical & Mechanical Properties	
Protective as needed	Bevel:
≥90	Clear Aperture (%):
45.00 x 45.00	Clear Aperture CA (mm):
50.00 x 50.00	Dimensions (mm):
3.30 ±0.2	Thickness (mm):
Seamed	Edges:
480.00	Knoop Hardness (kg/mm²):
0.20	Poisson's Ratio:
64	Young's Modulus (GPa):
50.00	Length (mm):
50.00	Width (mm):
Optical Properties	
65.41	Abbe Number (v _d):
NIR (700-1150nm)	Coating:
R _{avg} <1.0% @ 700 - 1150nm	Coating Specification:
1.472	Index of Refraction (n _d):
BOROFLOAT®	Substrate:
4 - 6λ	Surface Flatness (P-V):
80-50	Surface Quality:
≥97	Transmission (%):
700 - 1150	Wavelength Range (nm):
Material Properties	
3.25 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.23	Density (g/cm³):
525	Transformation Temperature (°C):
Environmental & Durability Factors	
1 hour @500; >100 hours @450	Operating Temperature (°C):
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	Resistance to Temperature Difference (K):
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	Thermal Shock (K):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

TECHNICAL INFORMATION



QUOTE YOUR SIZE

COMPATIBLE MOUNTS