

TECHSPEC<sup>®</sup> 450nm 12.5mm Diameter, OD 4.0 Shortpass Filter



High Performance OD 4.0 Shortpass Filters

Stock #84-691 ☐ In Stock

-

1

+

C\$264.60

ADD TO CART

Qty 1-5

C\$264.60

Qty 6+

C\$211.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
12.50 +0.0/-0.2

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥4.0

|                                                                                                                                                                                  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Cut-Off Wavelength (nm):</b><br>450.00                                                                                                                                        |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Coming 7980)                                |
| <b>Coating:</b><br>Hard Coated                                                                                                                                                   |
| <b>Rejection Wavelength (nm):</b><br>460 - 660                                                                                                                                   |
| <b>Surface Quality:</b><br>60-40                                                                                                                                                 |
| <b>Thickness (mm):</b><br>1.50                                                                                                                                                   |
| <b>Thickness Tolerance (mm):</b><br>±0.1                                                                                                                                         |
| <b>Transmission (%):</b><br>≥91                                                                                                                                                  |
| <b>Transmission Wavelength (nm):</b><br>300 - 441                                                                                                                                |
| <b>Type:</b><br>Shortpass Filter                                                                                                                                                 |
| <b>Clear Aperture (%):</b><br>>80                                                                                                                                                |
| <b>Transmitted Wavefront, RMS:</b><br>≤λ/4 @ 633nm (prior to coating)                                                                                                            |
| <b>Slope Factor (%):</b><br><1                                                                                                                                                   |
| <b>Cut-Off Tolerance (%):</b><br>±1                                                                                                                                              |
| <b>Environmental Durability:</b><br>Humidity per ML-STD-810H, Section 507.6<br>Temperature per ML-STD-810H, Section 501.7 and 502.7                                              |
| <b>Physical Durability:</b><br>Adhesion per ML-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per ML-PRF-13830B, Section C.4.5.11<br>Cleaning per ML-C-48497A Section 4.5.4.2 |
| <b>Note:</b><br>Arrow on part indicates filter coated surface.                                                                                                                   |
| <b>Wavelength Range (nm):</b><br>300 - 660                                                                                                                                       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |