

[See all 65 Products in Family](#)

Coherent® BioRay™ Laser 1264214 | 450nm, 50mW

See More by [Coherent®](#)



Stock #89-374 **1 In Stock**

1 C\$3,976⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$3,976.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Heat Dissipation of Laser Head:
5 W Max

Manufacturer:
Coherent®

Type of Laser:
Diode

IIIb Laser Class - CDRH:

1264214 Model Number:

Physical & Mechanical Properties

<70 Weight (g):

<10 Pointing Stability ($\mu\text{rad}/^\circ\text{C}$):

95.00 Length (mm):

Optical Properties

TEM_{00} Spatial Mode:

450.00 Wavelength (nm):

<1.5 Mode Quality, M^2 :

± 10 Wavelength Tolerance (nm):

<3 Output Beam Angle (mrad):

± 5 Beam Waist Position at Exit (mm):

2.4 x 0.8 Beam Diameter (mm):

0.4 x 0.8 Beam Divergence (mrad):

Blue Color:

Electrical

160 max @ 25°C Operating Current (mA):

50 Output Power (mW):

<2% (8 hours, $\pm 3^\circ\text{C}$) Power Stability (%):

Max Analog: 500
Rise Time (10% to 90%): <500 nsec
Fall Time (10% to 90%): <500 nsec
Modulation Frequency (kHz):

Level 4 ESD Protection:

20 Hz - 20 MHz <0.5%
20 Hz - 20 MHz peak-to-peak: <1%
RMS Noise:

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#86-878](#)
Europe: [#86-878](#)
Japan: [#86-878](#)
Korea: [#86-878](#)
China: [#86-878](#)

Free Space Output Type:

5 - 24 Input Voltage (V):

Threading & Mounting

Included Mount:

Environmental & Durability Factors

15 to 40 Operating Temperature ($^\circ\text{C}$):

-20 to +60 Storage Temperature ($^\circ\text{C}$):

30 G Shock Rating:

Regulatory Compliance

Exempt RoHS 2015:

Certificate of Conformance:

[View](#)

Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5□5V) with BNC connector is required.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
