

TECHSPEC® 45° AOI, 12.5mm Diameter, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock #64-443 **17 In Stock**

⊖ 1 ⊕ C\$71⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | C\$71.40 each |
| Qty 10-25 | C\$64.05 each |
| Qty 26-49 | C\$61.25 each |
| Need More? | Request Quote |

Product Downloads

General

Cold Mirror Type:

Physical & Mechanical Properties

12.50 Diameter (mm):

1.10 ±0.2 Thickness (mm):

Dimensional Tolerance (mm):

+0.0/-0.2

Optical Properties

Dichroic Filter **Transmission (%)**:

Dielectric **Coating Type**:

Cold Mirror, 45° **Coating**:

4 - 6λ **Surface Flatness (P-V)**:

425 - 1150 **Wavelength Range (nm)**:

Substrate:
BOROFLOAT®

45 **Angle of Incidence (°)**:

Coating Specification:
R_{avg} ≥95% @ 400 - 690nm and T_{avg} ≥90% @ 750 - 1200nm
AR Coating: R_{avg} <1% @ 700 - 1150nm

80-50 **Surface Quality**:

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View



Reach 247:
Compliant

Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information



Quote Your Size

Compatible Mounts