


[See all 5 Products in Family](#)

## 45° AOI 12.5mm Sq, Cold Mirror



Stock #62-634 CLEARANCE **20+ In Stock**

C\$16<sup>80</sup>

ADD TO CART

### Volume Pricing

Qty 1+	C\$16.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Cold Mirror Type:

### Physical & Mechanical Properties

1.10 Thickness (mm):

12.5 x 12.5 Dimensions (mm):

±0.5 Dimensional Tolerance (mm):

Length (mm):

12.50

Width (mm):

12.50

## Optical Properties

Dielectric **Coating Type:**

Cold Mirror, 45° **Coating:**

4 - 6λ **Surface Flatness (P-V):**

425 - 1200 **Wavelength Range (nm):**

**BOROFLOAT®** **Substrate:**

45.00 **Angle of Incidence (°):**

**Coating Specification:**  
R<sub>avg</sub> >90% @ 425 - 650nm  
T<sub>avg</sub> >85% @ 800 - 1200nm

80-50 **Surface Quality:**

## Regulatory Compliance



[View](#) **Certificate of Conformance:**

## Product Details

- 0° and 45° Angle of Incidence Options Available
- Reflects 90% of Visible Light
- Transmits 80% of the NIR and IR

These Cold Mirrors have a 0° and 45° angle of incidence and are ideal for decreasing the undesirable heat caused by infrared radiation. A multi-layer dielectric coating reflects 90% of visible light while transmitting over 80% of the NIR and IR. Cold Mirrors function satisfactorily with resistance to damage from ambient temperatures of -45°C to +232°C and are ideal for projection systems, where heat build-up can lead to system damage. Made of BOROFLOAT® glass, these Cold Mirrors can be cut to the desired size for any application.

## Technical Information



## Compatible Mounts