

TECHSPEC® 50.0mm Dia. x 125.0mm FL, NIR I, Inked, Plano-Convex Lens



Stock **#48-798-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 +

C\$98.70

ADD TO CART

Qty 1-9
C\$98.70
Qty 10+
C\$88.90
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):
125.00 @587.6nm

Back Focal Length BFL (mm): 118.39
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 10.00 ±0.10
Edge Thickness ET (mm): 4.97
Radius R₁ (mm): 64.60
Clear Aperture CA (mm): 49
f/#: 2.5
Numerical Aperture NA: 0.20
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View