

TECHSPEC® 4X, 532nm Scorpii® Nd:YAG Beam Expander



4X, 532nm LCht Fixed YAG Beam Expander, #37-053

Stock **#37-053** ☐ In Stock

-

1

+

C\$257.60

ADD TO CART

Qty 1-9

C\$257.60

Qty 10+

C\$228.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
VIS 0° (425-675nm)

Design Wavelength DWL (nm):
532

Entrance Aperture (mm): 5
Exit Aperture (mm): 10
Expansion Power: 4X
Substrate: ☐ Optical Glass
Length (mm): 58.60
Mounting Threads: M22 x0.75
Transmission (%): >98 (nominal)
Type: Beam Expander
Weight (g): 103
Housing Diameter (mm): 29.95
Transmitted Wavefront, P-V: <λ/4 @ 532nm for Input Beam ≤1.9mm (by design)
Coating Specification: Ravg ≤0.4% @ 425 - 675nm
Wavelength Range (nm): 532
Style: Fixed Magnification
Divergence Adjustment: None

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View