

50.8mm Dia, 450 - 650nm, $\lambda/2$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-035** ☐ In Stock

-

1

+

C\$4,368.00

ADD TO CART

Qty 1-5
C\$4,368.00
Qty 6+
C\$3,787.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
>34.0

Coating:
R_{avg} <0.75% @450 - 650nm

Diameter (mm):
50.80

Substrate: ☐

Crystal Quartz and MgF ₂
Retardance: λ/2
Surface Quality: 40-20
Thickness (mm): 6.00 ±0.2
Type: Achromatic Waveplate
Dimensional Tolerance (mm): +0/-0.25
Construction: Crystalline
Transmitted Wavefront, P-V: <λ/4 @ 632nm
Parallelism (arcsec): <10
Housing Tolerance (mm): +0/-0.25
Retardance Tolerance: λ/100 @ 20°C
Coating Specification: R _{avg} >0.75% @ 450 - 650nm
Wavelength Range (nm): 450 - 650
Damage Threshold, By Design: ☐ >5 J/cm ² @ 1064nm, 10ns, 10Hz
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant