


50.8mm Dia., 6mm Thick, 3-5µm BBAR Coated, ISP Optics Silicon (Si) Window | HDAR35-SI-W-50-6

See More by [ISP Optics](#)



Stock **#24-644** CLEARANCE **3 In Stock**

-

1

+

C\$191^{.77} ~~C\$383.53~~

ADD TO CART

Volume Pricing	
Qty 1+	C\$383.53 C\$191.77 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Protective Window

Type:

HDAR35-SI-W-50-6

Model Number:

Physical & Mechanical Properties	
Protective as needed	Bevel:
85	Clear Aperture (%):
43.18	Clear Aperture CA (mm):
50.80 +0.00/-0.13	Diameter (mm):
6.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
1,150.00	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.27	Poisson's Ratio:
140	Young's Modulus (GPa):
Optical Properties	
BBAR (3000-5000nm)	Coating:
R_{avg} <0.5% @ 3 - 5µm R_{abs} <1.5% @ 3 - 5µm	Coating Specification:
3.422 @ 5µm	Index of Refraction (n _d):
Silicon (Si)	Substrate:
2λ	Surface Flatness (P-V):
40-20	Surface Quality:
3000 - 5000	Wavelength Range (nm):
Material Properties	
2.55	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.33	Density (g/cm³):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Transmission from 1.2 - 7µm
- Available Uncoated or HDAR Coated for 3 - 5µm
- Ideal for Weight Sensitive Applications

ISP Optics Silicon (Si) Windows provide transmission in the Near-Infrared (NIR) and Mid-Wave Infrared (MMR) from 1.2 - 7µm. Silicon features a Knoop Hardness of 1150, making it harder and less brittle than Germanium. A High-Durability Anti-Reflection (HDAR) coating option increases the durability of the substrate while significantly improving transmission from 3 - 5µm, enabling use in harsh environments. ISP Optics Silicon (Si) Windows are ideal for weight-sensitive IR applications due to its low density of 2.329 g/cm³, which is half as dense as Germanium and Zinc Selenide. These windows are ideal for NIR imaging applications and are important for detection of sources radiating at a black body temperature of 700K.