

TECHSPEC® 50.0mm Dia. x 150.0mm FL, VIS-NIR Coated, Plano-Convex Lens



Stock **#45-718** ☐ In Stock
[Other Coating Options](#)

1

C\$95.20

ADD TO CART

Qty 1-9
C\$95.20
Qty 10+
C\$85.75
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):
150.00 @587.6nm

Back Focal Length BFL (mm): 144.07
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 9.00 ±0.10
Edge Thickness ET (mm): 4.86
Radius R₁ (mm): 77.52
Clear Aperture CA (mm): 49
f#: 3.00
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant