

50.8mm Dia. x 32mm FL, Aspheric Condenser Lens



Stock **#19-523** ☐ In Stock
[Other Coating Options](#)

1

C\$84.00

ADD TO CART

Qty 1-10
C\$84.00

Qty 11+
C\$75.60

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.80 +0.0/-0.2

Effective Focal Length EFL (mm):
32.00

Numerical Aperture NA:
0.79

Back Focal Length BFL (mm):

Substrate: □
H-K51

Focal Length Tolerance (%):
±5

Coating:
Uncoated

Centering (arcmin):
≤30

Surface Quality:
80-50 (typical)

Clear Aperture CA (mm):
45.72

Edge Thickness ET (mm):
2.10

Center Thickness CT (mm):
25.00 ±0.30

f#:
0.63

Bevel:
Protective bevel as needed

Diameter of Asphere (mm):
20.5

Radius R₂ (mm):
99.64

Shape of Back Surface:
Convex

Type:
Condenser Lens

Wavelength Range (nm):
350 - 2000

Conjugate Distance:
Infinite

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)