


[See all 389 Products in Family](#)

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#) / [Sapphire Windows](#)

TECHSPEC®

50.8mm Dia., 3.18mm Thick, BBAR (1650-3000nm) AR Coated Sapphire Window



Stock #15-999 **7 In Stock**

1 C\$763^{.00}

ADD TO CART

Volume Pricing	
Qty 1-24	C\$763.00 each
Qty 25-50	C\$579.60 each
Qty 51-99	C\$572.60 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
eDrawing:eprt	
EO Spec Sheet	Download All

General

Type: Protective Window	Type of Window: Crystal
--------------------------------	--------------------------------

Physical & Mechanical Properties

Clear Aperture CA (mm): 45.72	Diameter (mm): 50.80 ±0.05
Thickness (mm): 3.18 ±0.05	Parallelism (arcmin): ≤3.5
Bevel: Protective as needed	Clear Aperture (%): ≥90
Edges: Fine Ground	Poisson's Ratio: 0.27
Young's Modulus (GPa): 435	Knoop Hardness (kg/mm²): 1,900.00

Optical Properties

Coating: BBAR (1650-3000nm)	Substrate: Sapphire (Al ₂ O ₃)
Index of Refraction (n_d): 1.77	Surface Quality: 80-50
Abbe Number (v_d): 72.24	Surface Roughness (µm): 0.1 per Inch
Birefringence (n_o-n_e): 0.008 for Visible Light Orthogonal to Optical Axis	Axis Orientation: Random
Coating Specification: R _{avg} <1% @ 1650 - 3000nm	Wavelength Range (nm): 1650 - 3000

R_{abs} <2% @
1650 - 3000nm

Surface Flatness (P-V): 2λ (typical)

Material Properties

Density (g/cm³): 3.97

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 5.4 (Parallel to C-Axis)
4.3 (Perpendicular to C-Axis)

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: **View**

Reach 235: **Compliant**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Features Extreme Surface Hardness Chemical Resistance
- Transmits Wavelengths Ranging From UV to Mid-Infrared
- Thinner and Stronger than Standard Glass Windows
- Anti-Reflection Coating Options Covering 350 - 5000nm Available

TECHSPEC® Sapphire Windows are manufactured from single crystal sapphire, making them ideal for demanding applications (such as laser systems) because of their extreme surface hardness, high thermal conductivity, high dielectric constant and resistance to common chemical acids and alkalis. Sapphire is the second hardest crystal next to **diamond** and, because of their structural strength, sapphire windows can be made much thinner than other common windows with improved transmittance. Chemically, sapphire is single crystal aluminum oxide (Al₂O₃) and is useful in a transmission range from UV to mid-infrared or 330 - 5500nm when uncoated. TECHSPEC® Sapphire Windows are available with anti-reflection (AR) coatings to improve performance in the visible, NIR, and IR spectra with coating options covering 350 - 5000nm.

Technical Information

Related Products



Cage System Optical Lens Mounts




C, S, and T-Mount Circular Optic Mounts




PUROSOL™ Optical Cleaner

Frequently Purchased Together



























#39-270 - 50.8mm Dia.,
3.18mm Thick, NIR II AR Coated
Sapphire Window
C\$714.00



#16-013 - 50.8mm Dia., 3.18mm
Thick, BBAR (2000-5000nm) AR
Coated Sapphire Window
C\$756.00

Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
	50.8mm Optic Dia., Optic Mount	Fixed		#64-569	C\$68.95 Request Quote	12 In Stock <input type="text" value="1"/>
	9.5 - 73.0mm Optic Dia., Three-Screw Adjustable Ring Mount	Fixed		#36-605	C\$116.20 Request Quote	20+ In Stock <input type="text" value="1"/>
	50.0/50.8mm Optic Dia., E-Series Kinematic Mount	Adjustable - Tip-Tilt		#15-867	C\$134.40 Request Quote	CONTACT US <input type="text" value="1"/>
	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-530	C\$151.20 Request Quote	CONTACT US <input type="text" value="1"/>
	19.5 - 108.0mm Optic Dia., Three-Screw Adjustable Ring Mount	Fixed		#03-670	C\$159.60 Request Quote	20+ In Stock <input type="text" value="1"/>
	7.0 - 67.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-669	C\$162.40 Request Quote	20+ In Stock <input type="text" value="1"/>
	8.0 - 118.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-666	C\$168.00 Request Quote	20+ In Stock <input type="text" value="1"/>
	50.0/50.8mm Optic Dia., Optical Cell Assembly	Fixed		#36-465 CLEARANCE	C\$179.93 Request Quote	2 In Stock <input type="text" value="1"/>
	50.0/50.8mm Optic Dia., Kinematic Mount, 2-Screws	Adjustable - Tip-Tilt		#58-852	C\$189.00 Request Quote	20+ In Stock <input type="text" value="1"/>
	50.0/50.8mm Optic Dia., Kinematic Mount, 3-Screws	Adjustable - Tip-Tilt		#58-855	C\$219.80 Request Quote	20+ In Stock <input type="text" value="1"/>
	50.0/50.8mm Optic Dia., Stainless Steel Kinematic Mount, 2-Screws	Adjustable - Tip-Tilt		#26-816	C\$344.40 Request Quote	12 In Stock <input type="text" value="1"/>

	Title	Type	Compare	Stock Number	Price	Buy
 	50.0/50.8mm Optic Dia., Stainless Steel Kinematic Mount, 3-Screws	Adjustable - Tip-Tilt		#26-819	C\$375.20 Request Quote	CONTACT US <input type="text" value="1"/> 
 	50.0/50.8mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-957	C\$431.20 Request Quote	1 In Stock <input type="text" value="1"/> 
 	50.0/50.8mm Optic Dia., Kinematic Mirror Mount	Adjustable - Tip-Tilt		#55-005	C\$505.40 Request Quote	6 In Stock <input type="text" value="1"/> 
 	50.0/50.8mm Optic Dia., Kinematic Mirror Mount with Micrometer	Adjustable - Tip-Tilt		#56-326	C\$541.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-078	C\$574.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	50.0/50.8mm Optic Dia., Precision Gimbal Mount	Adjustable - Gimbal		#55-000	C\$714.00 Request Quote	7 In Stock <input type="text" value="1"/> 
 	50.0/50.8mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-960	C\$847.00 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	50.0/50.8mm Optic Dia., 5 Axes Optical Mount	Adjustable - Linear (XYZ) & Tip-Tilt		#13-778	C\$1,176.00 Request Quote	10 In Stock <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- Technical Tool
- Video
- Glossary
- FAQ

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

An Introduction to Optical Coatings

TECHNICAL TOOL

Beam Displacement Calculator

APPLICATION NOTE

Understanding Optical Windows

VIDEO

Optical Windows Review

APPLICATION NOTE

Optical Glass

[View More](#)
