

## 50mm Dia. 1000-2000nm, NIR Linear Polarizer



Stock **#48-890** ☐ In Stock

-

1

+

C\$735.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$735.00                     |
| Qty 6+                        |
| C\$627.20                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Coating:  
Uncoated

Diameter (mm):  
50.00

Extinction Ratio:  
1000:1

Substrate: ☐

|                                                           |
|-----------------------------------------------------------|
| Polymer Film on <a href="#">B270</a>                      |
| <b>Operating Temperature (°C):</b><br>-25 to +80          |
| <b>Thickness (mm):</b><br>2.00                            |
| <b>Thickness Tolerance (mm):</b><br>±0.2                  |
| <b>Transmission (%):</b><br>33.00                         |
| <b>Transmission Tolerance (%):</b><br>±3                  |
| <b>Type:</b><br>Linear Polarizer                          |
| <b>Parallelism (arcmin):</b><br><4                        |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2           |
| <b>Construction:</b><br>Dichroic Polarizing Film on Glass |
| <b>Wavelength Range (nm):</b><br>1000 - 2000              |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |