


[See all 22 Products in Family](#)

**TECHSPEC® 50.8mm Dia. Precision Broadband Laser Mirror Substrate**



TECHSPEC® Laser Mirror Substrates

Stock **#75-417** NEW **20+ In Stock**

C\$236<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1-5	C\$236.60 each
Qty 6-25	C\$207.90 each
Qty 26+	C\$182.70 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror Substrate Type:

**Physical & Mechanical Properties**

<3 Parallelism (arcmin):

90 Clear Aperture (%):

Ground	<b>Back Surface:</b>
50.80 +0.0/-0.1	<b>Diameter (mm):</b>
12.50 ±0.2	<b>Thickness (mm):</b>
Ground, protective bevel as needed	<b>Edges:</b>

## Optical Properties

10-5	<b>Surface Quality:</b>
λ/20	<b>Surface Flatness (P-V):</b>
Uncoated	<b>Coating:</b>
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- λ/10 and λ/20 Surface Flatness and 10-5 Surface Quality
- High Quality Fused Silica Substrates
- Imperial Sizes with Circular or Rectangular Geometries
- [Window Substrates](#) Also Available

TECHSPEC® Laser Mirror Substrates are manufactured from high quality fused silica and are designed for use with high power laser sources. These mirrors feature excellent surface specifications, including λ/10 and λ/20 surface flatness and 10-5 surface quality, to limit the possibility of reduced performance due to surface defects. The high surface quality of these mirror blanks also makes them ideal for use in demanding intra-cavity laser applications. TECHSPEC Laser Mirror Substrates are available in standard imperial sizes, with either circular or rectangular geometries. Please contact us if your application requires a custom size laser mirror substrate.