

TECHSPEC® 50mm, Aluminum & MgF₂ Coated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock **#45-397** ☐ In Stock

-

1

+

C\$323.40

ADD TO CART

Qty 1-5

C\$323.40

Qty 6+

C\$291.06

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
MgF₂ & Aluminized

Substrate: ☐
[N-BK7](#)

Surface Quality:
60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 70.70
Length of Legs (mm): 50.00
Image Orientation: Left-Handed
Coating Specification: Hypotenuse: R _{avg} >85% @ 400 - 700nm Legs: R _{avg} ≤1.75% @ 400 - 700nm
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/4
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @ 532nm & 1064nm, 10ns Legs: 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View