

TECHSPEC®

5.0mm Dia. x 10.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock **#47-869-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 +

C\$78.40

ADD TO CART

Qty 1-9
C\$78.40
Qty 10+
C\$70.70
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 ±0.025

Effective Focal Length EFL (mm):
10.00 @ 587.6nm

Back Focal Length BFL (mm): 8.91
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.64 ±0.05
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 5.17
Clear Aperture CA (mm): 4.5
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View