

50mm Dia. Ge, IR Holographic Wire Grid Polarizer



50mm Dia. Ge, IR Holographic Wire Grid Polarizer, #62-777

Stock **#62-777** ☐ In Stock

⊖ 1 ⊕ **C\$3,150.00**

ADD TO CART

Qty 1-5
C\$3,150.00
Qty 6+
C\$2,518.60
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
34.0

Diameter (mm):
50.00

Extinction Ratio: 300:1 @ 10.6µm
Substrate: ☐ Germanium (Ge)
Operating Temperature (°C): -20 to 75
Polarization: Notches on polarizer ring are aligned with wires of wire grid
Thickness (mm): 2.00
Transmission (%): >50
Type: Linear Polarizer
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Construction: Wire Grid
Groove Parallelism to Edge (°): N/A
Mount Thickness (mm): 6.0
Note: Notches on polarizer ring are aligned with wires of wire grid (max reflection)
Ring Thickness (mm): ±0.1
Wavelength Range (nm): 8000 - 17000
Surface Flatness (P-V): λ/20 @ 10.6 µm
Damage Threshold, By Design: ☐ 50 W/cm²
Mount: Black Anodized Aluminum
Groove Density (grooves/mm): 2700.00

Regulatory Compliance

RoHS: Compliant
Reach 219: Compliant
Certificate of Conformance: View