

**TECHSPEC® 50mm Dia. x 75mm FL, VIS 0°, Inked, Achromatic Lens**



Stock **#49-292-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 + **C\$266.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$266.00                     |
| Qty 6+                        |
| C\$212.80                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Diameter (mm):**  
50.00 ±0.025

**Effective Focal Length EFL (mm):**  
75.00

|                                                                                 |
|---------------------------------------------------------------------------------|
| <b>Focal Length Tolerance (%)</b> :<br>±1                                       |
| <b>Back Focal Length BFL (mm)</b> :<br>61.17                                    |
| <b>Focal Length Specification Wavelength (nm)</b> :<br>587.6                    |
| <b>Clear Aperture CA (mm)</b> :<br>49.00                                        |
| <b>Centering (arcmin)</b> :<br><1                                               |
| <b>Center Thickness CT (mm)</b> :<br>24.50 ±0.20                                |
| <b>Center Thickness CT 1 (mm)</b> :<br>20.00 ±0.10                              |
| <b>Center Thickness CT 2 (mm)</b> :<br>4.50 ±0.10                               |
| <b>Radius R<sub>1</sub> (mm)</b> :<br>51.88                                     |
| <b>Radius R<sub>2</sub> (mm)</b> :<br>-32.79                                    |
| <b>Radius R<sub>3</sub> (mm)</b> :<br>-309.45                                   |
| <b>Edge Thickness ET (mm)</b> :<br>17.07                                        |
| <b>Substrate</b> : <input type="checkbox"/><br><a href="#">N-BAF10 / N-SF10</a> |
| <b>Surface Quality</b> :<br>40-20                                               |
| <b>f/#</b> :<br>1.5                                                             |
| <b>Numerical Aperture NA</b> :<br>0.33                                          |
| <b>Coating</b> :<br>VIS 0° (425-675nm)                                          |
| <b>Coating Specification</b> :<br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm          |
| <b>Power (P-V) @ 632.8nm</b> :<br>1.5λ                                          |
| <b>Irregularity (P-V) @ 632.8nm</b> :<br>λ/4                                    |
| <b>Bevel</b> :<br>Protective bevel as needed                                    |
| <b>Type</b> :<br>Achromatic Lens                                                |
| <b>Wavelength Range (nm)</b> :<br>425 - 675                                     |

## Regulatory Compliance

|                                                             |
|-------------------------------------------------------------|
| <b>RoHS</b> :<br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance</b> :<br><a href="#">View</a> |