

TECHSPEC® 50mm Dia. x 75mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-389-INK** ☐ In Stock
[Other Coating Options](#)

1 **C\$285.60**

ADD TO CART

Qty 1-5
C\$285.60
Qty 6+
C\$228.55
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):
75.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 61.17
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 49.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 24.50 ±0.20
Center Thickness CT 1 (mm) : 20.00 ±0.10
Center Thickness CT 2 (mm) : 4.50 ±0.10
Radius R₁ (mm) : 51.88
Radius R₂ (mm) : -32.79
Radius R₃ (mm) : -309.45
Edge Thickness ET (mm) : 17.07
Substrate : ☐ N-BAF10 / N-SF10
Surface Quality : 40-20
f/# : 1.5
Numerical Aperture NA : 0.33
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View